

ZENFLOW-14


Ordering Information

Usable Length 100cm	Usable Length 130cm	Usable Length 140cm	Usable Length 150cm	Usable Length 180cm	Balloon Diameter [mm]	Balloon Length [mm]	NP [atm]	RBP [atm]
--	--	--	ZW150012501514B	ZW180012501514B	1.25	15	6	14
--	--	--	ZW150015001514B	ZW180015001514B	1.50			14
ZW100015002014B	--	--	ZW150015002014B	ZW180015002014B	1.50	20	6	16
--	ZW130015002014B	--	--	--	1.50			16
--	ZW130020002014B	--	--	--	2.00			16
--	ZW130025002014B	--	--	--	2.50			16
--	ZW130030002014B	--	--	--	3.00			16
--	ZW130035002014B	--	--	--	3.50			16
--	ZW130040002014B	--	--	--	4.00			16
--	ZW130050002014B	--	--	--	5.00			14
--	ZW130015003014B	--	--	--	1.50			16
--	ZW130020003014B	--	--	--	2.00			16
--	ZW130025003014B	--	--	--	2.50			16
--	ZW130030003014B	--	--	--	3.00			16
--	ZW130035003014B	--	--	--	3.50			16
--	ZW130040003014B	--	--	--	4.00			16
--	ZW130050003014B	--	--	--	5.00			14
ZW100015004014B	ZW130015004014B	--	ZW150015004014B	ZW180015004014B	1.50			16
ZW100020004014B	ZW130020004014B	ZW140020004014B	ZW150020004014B	ZW180020004014B	2.00			16
ZW100025004014B	ZW130025004014B	ZW140025004014B	ZW150025004014B	ZW180025004014B	2.50			16
ZW100030004014B	ZW130030004014B	ZW140030004014B	ZW150030004014B	ZW180030004014B	3.00			16
ZW100035004014B	ZW130035004014B	ZW140035004014B	ZW150035004014B	ZW180035004014B	3.50			16
ZW100040004014B	ZW130040004014B	ZW140040004014B	ZW150040004014B	ZW180040004014B	4.00			16
ZW100050004014B	ZW130050004014B	ZW140050004014B	ZW150050004014B	ZW180050004014B	5.00			14
--	ZW130015006014B	--	--	--	1.50			16
--	ZW130020006014B	--	--	--	2.00			15
--	ZW130025006014B	--	--	--	2.50			15
--	ZW130030006014B	--	--	--	3.00			15
--	ZW130035006014B	--	--	--	3.50			15
--	ZW130040006014B	--	--	--	4.00			15
--	ZW130050006014B	--	--	--	5.00			13
ZW100015008014B	ZW130015008014B	--	ZW150015008014B	ZW180015008014B	1.50			16
ZW100020008014B	ZW130020008014B	ZW140020008014B	ZW150020008014B	ZW180020008014B	2.00			15
ZW100025008014B	ZW130025008014B	ZW140025008014B	ZW150025008014B	ZW180025008014B	2.50			15
ZW100030008014B	ZW130030008014B	ZW140030008014B	ZW150030008014B	ZW180030008014B	3.00			15
ZW100035008014B	ZW130035008014B	ZW140035008014B	ZW150035008014B	ZW180035008014B	3.50			15
ZW100040008014B	ZW130040008014B	ZW140040008014B	ZW150040008014B	ZW180040008014B	4.00			15
ZW100050008014B	ZW130050008014B	ZW140050008014B	ZW150050008014B	ZW180050008014B	5.00			13
ZW100015010014B	ZW130015010014B	--	ZW150015010014B	ZW180015010014B	1.50			16
ZW100020010014B	ZW130020010014B	ZW140020010014B	ZW150020010014B	ZW180020010014B	2.00			15
ZW100025010014B	ZW130025010014B	ZW140025010014B	ZW150025010014B	ZW180025010014B	2.50			15
ZW100030010014B	ZW130030010014B	ZW140030010014B	ZW150030010014B	ZW180030010014B	3.00			15
ZW100035010014B	ZW130035010014B	ZW140035010014B	ZW150035010014B	ZW180035010014B	3.50			15
ZW100040010014B	ZW130040010014B	ZW140040010014B	ZW150040010014B	ZW180040010014B	4.00			15
ZW100050010014B	ZW130050010014B	ZW140050010014B	ZW150050010014B	ZW180050010014B	5.00			13
ZW100015012014B	ZW130015012014B	--	ZW150015012014B	ZW180015012014B	1.50			16
ZW100020012014B	ZW130020012014B	ZW140020012014B	ZW150020012014B	ZW180020012014B	2.00			15
ZW100025012014B	ZW130025012014B	ZW140025012014B	ZW150025012014B	ZW180025012014B	2.50			15
ZW100030012014B	ZW130030012014B	ZW140030012014B	ZW150030012014B	ZW180030012014B	3.00			15
ZW100035012014B	ZW130035012014B	ZW140035012014B	ZW150035012014B	ZW180035012014B	3.50			15
ZW100040012014B	ZW130040012014B	ZW140040012014B	ZW150040012014B	ZW180040012014B	4.00			15
ZW100050012014B	ZW130050012014B	ZW140050012014B	ZW150050012014B	ZW180050012014B	5.00			13
ZW100020015014B	ZW130020015014B	ZW140020015014B	ZW150020015014B	ZW180020015014B	2.00			15
ZW100025015014B	ZW130025015014B	ZW140025015014B	ZW150025015014B	ZW180025015014B	2.50			15
ZW100030015014B	ZW130030015014B	ZW140030015014B	ZW150030015014B	ZW180030015014B	3.00			15
--	--	ZW140035015014B	--	--	3.50			15
--	--	ZW140040015014B	--	--	4.00			15
--	--	ZW140050015014B	--	--	5.00			13
ZW100020022014B	ZW130020022014B	ZW140020022014B	ZW150020022014B	ZW180020022014B	2.00			15
ZW100025022014B	ZW130025022014B	ZW140025022014B	ZW150025022014B	ZW180025022014B	2.50			15
ZW100030022014B	ZW130030022014B	ZW140030022014B	ZW150030022014B	ZW180030022014B	3.00			15
--	--	ZW140035022014B	--	--	3.50			15
--	--	ZW140040022014B	--	--	4.00			15
--	--	ZW140050022014B	--	--	5.00			13



ZENFLOW™

PTA Balloon Catheter



Easy Access to The Most Challenging Anatomies

Company Information

Zylox Medical Device Co.,Ltd was founded in the beautiful city of Hangzhou in 2012 by a group of highly skillful and experienced returnees from the US and Europe. They have on average 5-20 years of working experiences in various functional areas such as research and development, management, and manufacturing in leading device makers including Johnson & Johnson, Medtronic, and Abbott before returning to China.

Since its inception, Zylox has developed an increasingly rich product pipeline of interventional and implantable peripheral vascular devices such as PTA balloons, PTA drug-coated Balloons (PTA DCB), superficial femoral artery (SFA) stent, drug-eluting SFA stent, and other vascular accessories. Zylox is also in the process of developing other sophisticated vascular devices such as covered stents and vena cava filters.

Zylox is certified by TUV accordingly to ISO 13485 standard. Many of its products including PTA balloons and SFA stent are also certified with CE Marks. Zylox strives to continuously innovate and provide patients with high quality medical devices.

Innovate
Mission
Quality

ZENFLOW-35

Excellent 6 wings
Folding and Re-
folding



guarantee low crossing profile and
with durable hydrophilic coating
optimize balloon crossability


Dual-lumen Shaft
Design



minimizes shaft OD while maintain-
ing a large inner lumen for quick
inflation and deflation times


Score-Flex Bal-
loon Material

reduces balloon wall thickness
without compromising RBP and
enhances kink resistance



Product Specification

Catheter Type	Over-The-Wire (OTW)
Guidewire	0.035"
Catheter Tip	Flexible, short and cone-shaped
Balloon Material	Nylon
Folding	Three/six wings
Coating	Hydrophilic coating
Marker	2
Balloon Size	Diameter: 2.0~12.0mm ; Length: 20~220mm
Shaft	4~8F
Usable Length	75, 100, 110 and 130cm



ZENFLOW-18

Low Entry Profile and Excellent Flexibility


conform the product to various anatomies and natural vessel tortuosity

Low Profile Introducer Sheath

results in lower possibility of puncture trauma


Specially-processed Delivery System

reduces kinking, achieves a greater pushability and allows you to treat your patients more effectively



Product Specification

Catheter Type	Over-The-Wire (OTW)
Guidewire	0.018"
Catheter Tip	Flexible, short and cone-shaped
Balloon Material	Nylon
Folding	Three/six wings
Coating	Hydrophilic coating
Marker	2
Balloon Size	Diameter: 2.0~9.0mm ; Length: 20~220mm
Shaft	4~6F
Usable Length	45, 75, 90, 130, 150 and 180cm



ZENFLOW-14

The Broadest Range of Sizes


provides the most comprehensive solution for below-the-knee(BTK) lesions

Advanced Crossability and Pushability

contribute to outstanding balloon performances


Long lengths up to 220mm

The design of long tapered tip enables you to achieve satisfactory outcomes for the most difficult distal lesions



Product Specification

Catheter Type	Over-The-Wire (OTW)
Guidewire	0.014"
Catheter Tip	Flexible, short and cone-shaped
Balloon Material	Nylon
Folding	Three wings
Coating	Hydrophilic coating
Marker	2
Balloon Size	Diameter: 1.25-5.0mm; Length: 15-220mm
Shaft	4F
Usable Length	100, 130, 140, 150 and 180cm



ZENFLOW-35

Ordering Information

ZENFLOW-18

Ordering Information

Usable Length 75cm	Usable Length 100cm	Usable Length 110cm	Usable Length 130cm	Balloon Diameter [mm]	Balloon Length [mm]	NP [atm]	RBP [atm]
--	--	ZW110020002035B	--	2.00	20	6	16
--	--	ZW110025002035B	--	2.50			16
ZW075030002035B	ZW100030002035B	ZW110030002035B	ZW130030002035B	3.00			16
ZW075035002035B	--	ZW110035002035B	--	3.50			16
ZW075040002035B	ZW100040002035B	ZW110040002035B	ZW130040002035B	4.00			16
ZW075050002035B	ZW100050002035B	ZW110050002035B	ZW130050002035B	5.00			14
ZW075060002035B	ZW100060002035B	--	ZW130060002035B	6.00			13
ZW075070002035B	ZW100070002035B	--	ZW130070002035B	7.00			12
ZW075080002035B	ZW100080002035B	--	ZW130080002035B	8.00			12
ZW075090002035B	ZW100090002035B	--	--	9.00			11
ZW075100002035B	ZW100100002035B	--	--	10.00			11
ZW075120002035B	ZW100120002035B	--	--	12.00			10
--	--	ZW110020004035B	--	2.00	40	6	16
--	--	ZW110025004035B	--	2.50			16
ZW075030004035B	ZW100030004035B	ZW110030004035B	ZW130030004035B	3.00			16
ZW075035004035B	--	ZW110035004035B	--	3.50			16
ZW075040004035B	ZW100040004035B	ZW110040004035B	ZW130040004035B	4.00			16
ZW075050004035B	ZW100050004035B	ZW110050004035B	ZW130050004035B	5.00			14
ZW075060004035B	ZW100060004035B	--	ZW130060004035B	6.00			13
ZW075070004035B	ZW100070004035B	--	ZW130070004035B	7.00			12
ZW075080004035B	ZW100080004035B	--	ZW130080004035B	8.00			12
ZW075090004035B	ZW100090004035B	--	--	9.00			11
ZW075100004035B	ZW100100004035B	--	--	10.00			11
ZW075120004035B	ZW100120004035B	--	--	12.00			10
--	--	ZW110020006035B	--	2.00	60	6	16
--	--	ZW110025006035B	--	2.50			16
ZW075030006035B	ZW100030006035B	ZW110030006035B	ZW130030006035B	3.00			16
ZW075035006035B	--	ZW110035006035B	--	3.50			16
ZW075040006035B	ZW100040006035B	ZW110040006035B	ZW130040006035B	4.00			16
ZW075050006035B	ZW100050006035B	ZW110050006035B	ZW130050006035B	5.00			14
ZW075060006035B	ZW100060006035B	--	ZW130060006035B	6.00			13
ZW075070006035B	ZW100070006035B	--	ZW130070006035B	7.00			12
ZW075080006035B	ZW100080006035B	--	ZW130080006035B	8.00			12
ZW075090006035B	ZW100090006035B	--	--	9.00			11
ZW075100006035B	ZW100100006035B	--	--	10.00			11
--	--	ZW110020008035B	--	2.00	80	6	15
--	--	ZW110025008035B	--	2.50			15
ZW075030008035B	ZW100030008035B	ZW110030008035B	ZW130030008035B	3.00			15
ZW075035008035B	--	ZW110035008035B	--	3.50			15
ZW075040008035B	ZW100040008035B	ZW110040008035B	ZW130040008035B	4.00			15
ZW075050008035B	ZW100050008035B	--	ZW130050008035B	5.00			13
ZW075060008035B	ZW100060008035B	--	ZW130060008035B	6.00			12
--	--	ZW110020010035B	--	2.00			15
--	--	ZW110025010035B	--	2.50			15
ZW075030010035B	ZW100030010035B	ZW110030010035B	ZW130030010035B	3.00			15
ZW075035010035B	--	ZW110035010035B	--	3.50	100	6	15
ZW075040010035B	ZW100040010035B	ZW110040010035B	ZW130040010035B	4.00			15
ZW075050010035B	ZW100050010035B	ZW110050010035B	ZW130050010035B	5.00			13
ZW075060010035B	ZW100060010035B	--	ZW130060010035B	6.00			12
--	--	ZW110020012035B	--	2.00			15
--	--	ZW110025012035B	--	2.50			15
ZW075030012035B	ZW100030012035B	ZW110030012035B	ZW130030012035B	3.00			15
ZW075035012035B	--	ZW110035012035B	--	3.50			15
ZW075040012035B	ZW100040012035B	ZW110040012035B	ZW130040012035B	4.00			15
ZW075050012035B	ZW100050012035B	ZW110050012035B	ZW130050012035B	5.00			13
ZW075060012035B	ZW100060012035B	--	ZW130060012035B	6.00			12
--	--	ZW110020015035B	--	2.00	120	6	15
--	--	ZW110025015035B	--	2.50			15
ZW075030015035B	ZW100030015035B	ZW110030015035B	ZW130030015035B	3.00			15
ZW075035015035B	--	ZW110035015035B	--	3.50			15
ZW075040015035B	ZW100040015035B	ZW110040015035B	ZW130040015035B	4.00			15
ZW075050015035B	ZW100050015035B	--	ZW130050015035B	5.00			13
ZW075060015035B	ZW100060015035B	--	ZW130060015035B	6.00			12
--	--	ZW110020022035B	--	2.00			15
--	--	ZW110025022035B	--	2.50			15
ZW075030022035B	ZW100030022035B	ZW110030022035B	ZW130030022035B	3.00			15
ZW075035022035B	--	ZW110035022035B	--	3.50	150	6	15
ZW075040022035B	ZW100040022035B	ZW110040022035B	ZW130040022035B	4.00			15
ZW075050022035B	ZW100050022035B	--	ZW130050022035B	5.00			13
ZW075060022035B	ZW100060022035B	--	ZW130060022035B	6.00			12
--	--	ZW110020025035B	--	2.00	220	6	15
--	--	ZW110025025035B	--	2.50			15
ZW075030025035B	ZW100030025035B	ZW110030025035B	ZW130030025035B	3.00			15
ZW075035025035B	--	ZW110035025035B	--	3.50			15
ZW075040025035B	ZW100040025035B	ZW110040025035B	ZW130040025035B	4.00			15
ZW075050025035B	ZW100050025035B	--	ZW130050025035B	5.00			13
ZW075060025035B	ZW100060025035B	--	ZW130060025035B	6.00			12
--	--	ZW110020028035B	--	2.00			15
--	--	ZW110025028035B	--	2.50			15
ZW075030028035B	ZW100030028035B	ZW110030028035B	ZW130030028035B	3.00			15
ZW075035028035B	--	ZW110035028035B	--	3.50			15

Usable Length 45cm	Usable Length 75cm	Usable Length 90cm	Usable Length 130cm	Usable Length 150cm	Usable Length 180cm	Balloon Diameter [mm]	Balloon Length [mm]	NP [atm]	RBP [atm]
--	ZW075020002018B	--	ZW130020002018B	--	--	2.00	20	6	16
--	ZW075025002018B	--	ZW130025002018B	--	--	2.50			16
--	ZW075030002018B	--	ZW130030002018B	--	--	3.00			16
--	ZW075035002018B	--	ZW130035002018B	--	--	3.50			16
--	ZW075040002018B	--	ZW130040002018B	--	--	4.00			16
--	ZW075050002018B	--	ZW130050002018B	--	--	5.00			14
--	ZW075060002018B	--	ZW130060002018B	--	--	6.00			14
--	ZW075020004018B	ZW090020004018B	ZW130020004018B	--	ZW180020004018B	2.00	40	6	16
--	ZW075025004018B	ZW090025004018B	ZW130025004018B	--	ZW180025004018B	2.50			16
--	ZW075030004018B	ZW090030004018B	ZW130030004018B	--	ZW180030004018B	3.00			16
--	ZW075035004018B	--	ZW130035004018B	--	ZW180035004018B	3.50			16
--	ZW075040004018B	--	ZW130040004018B	--	ZW180040004018B	4.00			16
ZW045050004018B	ZW075050004018B	--	ZW130050004018B	ZW150050004018B	ZW180050004018B	5.00			14
ZW045060004018B	ZW075060004018B	--	ZW130060004018B	ZW150060004018B	ZW180060004018B	6.00	60	6	14
ZW045070004018B	ZW075070004018B	--	ZW130070004018B	ZW150070004018B	ZW180070004018B	7.00			12
--	ZW075080004018B	--	ZW130080004018B	--	--	8.00			12
--	ZW075090004018B	--	ZW130090004018B	--	--	9.00			11
--	ZW075020006018B	--	ZW130020006018B	--	--	2.00			16
--	ZW075025006018B	--	ZW130025006018B	--	--	2.50	80	6	16
--	ZW075030006018B	--	ZW130030006018B	--	--	3.00			16
--	ZW075035006018B	--	ZW130035006018B	--	--	3.50			16
--	ZW075040006018B	--	ZW130040006018B	--	--	4.00			16
ZW045050006018B	ZW075050006018B	--	ZW130050006018B	--	--	5.00			14
ZW045060006018B	ZW075060006018B	--	ZW130060006018B	--	--	6.00			14
ZW045070006018B	ZW075070006018B	--	ZW130070006018B	--	--	7.00	100	6	12
--	ZW075080006018B	--	ZW130080006018B	--	--	8.00			12
--	ZW075090006018B	--	ZW130090006018B	--	--	9.00			11
--	ZW075020008018B	ZW090020008018B	ZW130020008018B	--	ZW180020008018B	2.00			15
--	ZW075025008018B	ZW090025008018B	ZW130025008018B	--	ZW180025008018B	2.50			15
--	ZW075030008018B	ZW090030008018B	ZW130030008018B	--	ZW180030008018B	3.00	120	6	15
--	ZW075035008018B	--	ZW130035008018B	--	ZW180035008018B	3.50			15
--	ZW075040008018B	--	ZW130040008018B	--	ZW180040008018B	4.00			15
--	ZW075050008018B	--	ZW130050008018B	ZW150050008018B	ZW180050008018B	5.00			13
--	ZW075060008018B	--	ZW130060008018B	ZW150060008018B	ZW180060008018B	6.00			12
--	--	--	--	ZW150070008018B	ZW180070008018B	7.00			12
--	ZW075020010018B	--	ZW130020010018B	--	ZW180020010018B	2.00	150	6	15
--	ZW075025010018B	--	ZW130025010018B	--	ZW180025010018B	2.50			15
--	ZW075030010018B	--	ZW130030010018B	--	ZW180030010018B	3.00			15
--	ZW075035010018B	--	ZW130035010018B	--	ZW180035010018B	3.50			15
--	ZW075040010018B	--	ZW130040010018B	--	ZW180040010018B	4.00			